

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P560302-192 Point Dume-Dunemere

Jeffrey Alan Marks Point Dume Dunemere Shelter White Outdoor Wall Lantern

**Category:** Outdoor

**Finish:** Shelter White (Painted)

**Construction:** EPMM Construction

**Glass/Shade:** Clear Glass Flat Square/Rectangular, Clear Glass Panel



Width: 6-5/8 in  
Extends: 5-7/8 in  
Height: 10-1/2 in  
H/CTR: 7-5/8 in

Clear Glass Flat Square/Rectangular  
Width: 4-1/8 in  
Height: 6-7/16 in

Clear Glass Panel  
Width: 4-1/2 in  
Height: 8-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type T10	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.625" W., 8.875" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	