

Project:			
Fixture Type:			
Location:			
Contact:			

## P560302-31M

## **Point Dume-Dunemere**

Jeffrey Alan Marks Point Dume Dunemere Matte Black Outdoor Wall Lantern

Category: Outdoor

Finish: Matte Black (Painted)
Construction: EPMM Construction

Glass/Shade: Clear Glass Flat Square/Rectangular, Clear Glass Panel



Width: 6-5/8 in Extends: 5-7/8 in Height: 10-1/2 in H/CTR: 7-5/8 in

Clear Glass Flat Square/Rectangular

Width: 4-1/8 in Height: 6-7/16 in

Clear Glass Panel Width: 4-1/2 in Height: 8-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type T10	5-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.625" W., 8.875" ht., 0.75" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	