

Project:

Fixture Type:

Location:

Contact:

P560303-141 Point Dume-Dunemere

Jeffrey Alan Marks Point Dume Dunemere Galvanized Finish Outdoor Wall Lantern

Category: Outdoor

Finish: Galvanized Finish (Painted) **Construction:** EPMM Construction

Glass/Shade: Clear Glass Flat Square/Rectangular, Clear Glass Panel



Width: 6-5/8 in Extends: 5-7/8 in Height: 14 in H/CTR: 9-1/4 in

Clear Glass Flat Square/Rectangular

Width: 4-1/8 in Height: 9-7/8 in

Clear Glass Panel Width: 4-1/2 in Height: 12-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type T10	5-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.75" W., 12.25" ht., 0.75" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	