

Project:

Fixture Type:

Location:

Contact:

## P560304-192

## **Point Dume-Dunemere**

Jeffrey Alan Marks Point Dume Dunemere Shelter White Outdoor Wall Lantern

Category: Outdoor

**Finish:** Shelter White (Painted) **Construction:** EPMM Construction

Glass/Shade: Clear Glass Flat Square/Rectangular, Clear Glass Panel



Width: 8 in Extends: 7-1/8 in Height: 16 in H/CTR: 10-1/8 in

Clear Glass Flat Square/Rectangular

Width: 5-1/8 in Height: 11-1/16 in

Clear Glass Panel Width: 5-3/16 in Height: 14-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type T10	5-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5.81" W., 13.9375" ht., 0.875" depth		LED: 12.5-watt MAX per socket	
,		Fully dimmable with dimmable bulbs	