

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P560304-31M Point Dume-Dunemere

Jeffrey Alan Marks Point Dume Dunemere Matte Black Outdoor Wall Lantern

**Category:** Outdoor  
**Finish:** Matte Black (Painted)  
**Construction:** EPMM Construction  
**Glass/Shade:** Clear Glass Flat Square/Rectangular, Clear Glass Panel



Width: 8 in  
Extends: 7-1/8 in  
Height: 16 in  
H/CTR: 10-1/8 in

Clear Glass Flat Square/Rectangular  
Width: 5-1/8 in  
Height: 11-1/16 in

Clear Glass Panel  
Width: 5-3/16 in  
Height: 14-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type T10	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.81" W., 13.9375" ht., 0.875" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	