

Project:		
Fixture Type:		
Location:		
Contact:		

P560305-141 Point Dume-Hook Pond

Jeffrey Alan Marks Point Dume Hook Pond Galvanized Finish Outdoor Wall Lantern

Category: Outdoor

Finish: Galvanized Finish (Painted) **Construction:** EPMM Construction

Glass/Shade: Clear with Silver Mesh Print Glass Flat Square/Rectangular,

Clear with Silver Mesh Print Glass Flat Square/Rectangular



Width: 6-1/4 in Extends: 5-1/4 in Height: 16-1/2 in H/CTR: 11 in

Clear with Silver Mesh Print Glass Flat Square/Rectangular

Width: 4-1/2 in Height: 8-7/8 in

Clear with Silver Mesh Print Glass Flat Square/Rectangular

Width: 3-3/8 in Height: 8-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type G-25	5-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.56" W., 10.5" ht., 0.8125" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	