

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560306-141 Point Dume-Hook Pond

Jeffrey Alan Marks Point Dume Hook Pond Galvanized Finish Outdoor Wall Lantern

Category: Outdoor

Finish: Galvanized Finish (Painted)

Construction: EPMM Construction

Glass/Shade: Clear with Silver Mesh Print Glass Flat Square/Rectangular, Clear with Silver Mesh Print Glass Flat Square/Rectangular



Width: 8-1/2 in
Extends: 7-1/8 in
Height: 22-3/8 in
H/CTR: 15-1/8 in

Clear with Silver Mesh Print Glass Flat Square/Rectangular
Width: 6-1/4 in
Height: 11-7/8 in

Clear with Silver Mesh Print Glass Flat Square/Rectangular
Width: 4-3/4 in
Height: 11-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type G-25	5-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 6.31" W., 14.125" ht., 1.06" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	