



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560308-020 Padgett

Padgett Collection One-Light Transitional Antique Bronze Clear Seeded Glass
Outdoor Wall Lantern

Category: Outdoor

Finish: Antique Bronze (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Clear Seeded Glass Panel



Width: 8 in
Extends: 9-5/8 in
Height: 15 in
H/CTR: 11-3/8 in

Clear Seeded Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.31" W., 6.62" ht., 1.12" depth		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket Fully dimmable with dimmable bulbs	