

Project:			
Fixture Type:			
Location:			
Contact:			

P560309-020

Padgett

Padgett Collection One-Light Transitional Antique Bronze Clear Seeded Glass Outdoor Wall Lantern

Category: Outdoor

Finish: Antique Bronze (Painted)

Construction: Cast Aluminum Construction **Glass/Shade:** Clear Seeded Glass Panel



Width: 10 in Extends: 11-3/4 in Height: 18-7/8 in H/CTR: 14-1/2 in

Clear Seeded Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4"		Incandescent: 100-watt MAX per	
recessed outlet box: 5.56" W., 8.25" ht., 1.12" depth		LED: 17.5-watt MAX per socket	
, ,		Fully dimmable with dimmable bulbs	