

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560316-031
Birkdale

Birkdale Collection One-Light Modern Farmhouse Textured Black Outdoor Wall Lantern

Category: Outdoor

Finish: Textured Black (Painted)

Construction: Cast Aluminum Construction



Width: 5-3/4 in
Extends: 8-1/4 in
Height: 18-3/8 in
H/CTR: 12-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W., 8.75" ht., 0.87" depth		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket Fully dimmable with dimmable bulbs	Dark Sky compliant