

Project:			
Fixture Type:			
Location:			
Contact:			

## P560317-020

## **Birkdale**

Birkdale Collection One-Light Modern Farmhouse Antique Bronze Outdoor Wall Lantern

Category: Outdoor

Finish: Antique Bronze (Painted)

Construction: Cast Aluminum Construction



Width: 7 in Extends: 9-1/2 in Height: 23-1/4 in H/CTR: 17 in

	,				
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION		
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed		
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty		
Canopy covers a standard 4" recessed outlet box: 4.75" W., 8.75" ht., 0.87" depth		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	Dark Sky compliant		
,		Fully dimmable with dimmable bulbs			