

Project:			
Fixture Type:			
Location:			
Contact:			

P560321-020 Dillard

Dillard Collection One-Light Traditional Antique Bronze Clear Glass Outdoor Wall Lantern

Category: Outdoor

Finish: Antique Bronze (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Clear Glass Panel



Width: 6-1/2 in Extends: 6-3/8 in Height: 11-3/8 in H/CTR: 8-3/8 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy 4.5" W., 7" ht., 0.81"		Incandescent: 60-watt MAX per socket	
depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	