

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560322-031
Dillard

Dillard Collection One-Light Traditional Textured Black Clear Glass Outdoor Wall Lantern

Category: Outdoor
Finish: Textured Black (Painted)
Construction: Cast Aluminum Construction
Glass/Shade: Clear Glass Panel



Width: 8-1/8 in
Extends: 7-7/8 in
Height: 15-1/2 in
H/CTR: 8-7/8 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy 4.5" W., 7" ht., 0.81" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	