

Project:			
Fixture Type:			
Location:			
Contact:			

P560323-020 Dillard

Dillard Collection One-Light Traditional Antique Bronze Clear Glass Outdoor Wall Lantern

Category: Outdoor

Finish: Antique Bronze (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Clear Glass Panel



Width: 9-3/4 in Extends: 9-1/2 in Height: 18-1/8 in H/CTR: 10-1/2 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy 5" W., 9.25" ht., 1" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	