

Project:			
Fixture Type:			
Location:			
Contact:			

P560333-31M

Stallworth

Stallworth Collection One-Light Matte Black Contemporary Outdoor Medium Wall Lantern

Category: Outdoor

Finish: Matte Black (Painted) **Construction:** Steel Construction

Glass/Shade: Matte Black Metal Cylindrical



Width: 6.5 in Extends: 8 in Height: 12.5 in H/CTR: 5-3/4 in

Matte Black Metal Cylindrical

		<u> </u>	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 5.5" ht., 0.75" depth		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	Yes, per photometry (not registered with IDA)
ne, cho dopen		Fully dimmable with dimmable bulbs	