

Project:		
Fixture Type:		
Location:		
Contact:		

P560334-31M

Stallworth

Stallworth Collection One-Light Matte Black Contemporary Outdoor Large Wall Lantern

Category: Outdoor

Finish: Matte Black (Painted)
Construction: Steel Construction

Glass/Shade: Matte Black Metal Cylindrical



Width: 9 in Extends: 11 in Height: 18 in H/CTR: 8-3/4 in

Matte Black Metal Cylindrical

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 6.37" W., 7.87" ht., 0.75" depth		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	Yes, per photometry (not registered with IDA)
		Fully dimmable with dimmable bulbs	