

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P560335-020
Hutchence

Hutchence Collection One-Light Antique Bronze with Antique Copper Transitional Outdoor Medium Wall Lantern

Category: Outdoor
Finish: Antique Bronze (Painted) with Antique Copper accent
Construction: Steel Construction
Glass/Shade: Antique Copper Metal Cone



Width: 6-3/4 in
 Extends: 5-3/4 in
 Height: 12 in
 H/CTR: 6-1/4 in

Antique Copper Metal Cone

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cCSAus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 5.5" ht., 0.81" depth		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket Fully dimmable with dimmable bulbs	Yes, per photometry (not registered with IDA)