



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P560336-020 Hutchence

Hutchence Collection One-Light Antique Bronze with Antique Copper Transitional Outdoor Large Wall Lantern

Category: Outdoor

Finish: Antique Bronze (Painted) with Antique Copper accent

Construction: Steel Construction

Glass/Shade: Antique Copper Metal Cone



Width: 9.5 in
Extends: 8-3/8 in
Height: 18 in
H/CTR: 10 in

Antique Copper Metal Cone

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 6.68" ht., 0.75" depth		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket Fully dimmable with dimmable bulbs	Yes, per photometry (not registered with IDA)