

Project:

Fixture Type:

Location:

Contact:

## P560338-031

## Ramsey

Ramsey Collection Textured Black Modern Farmhouse Outdoor Medium Wall Lantern

Category: Outdoor

Finish: Textured Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Panel



Width: 7-1/2 in Extends: 7-3/8 in Height: 15-1/2 in H/CTR: 3-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cCSAus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.5" W., 5.5" ht., 0.75" depth		LED: 12.5-watt MAX per socket	
•		Fully dimmable with dimmable bulbs	