

Project:			
Fixture Type:			
Location:			
Contact:			

P560339-031

Ramsey

Ramsey Collection Textured Black Modern Farmhouse Outdoor Large Wall Lantern

Category: Outdoor

Finish: Textured Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Panel



Width: 9 in Extends: 8-5/8 in Height: 18-1/2 in H/CTR: 3-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Candelabra Base (E12) Socket	cCSAus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4"		Incandescent: 60-watt MAX per socket	
recessed outlet box: 4.5" W., 5.5" ht., 0.75" depth		LED: 12.5-watt MAX per socket	
,		Fully dimmable with dimmable bulbs	