## PROGRESS LIGHTING

Project:	 	
Fixture Type:		
Location:		

Contact:

## **P560340-31M** Keegan

Keegan Collection One-Light Matte Black Clear Glass Coastal Outdoor Wall Lantern

Category: Outdoor Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Width: 7-1/4 in Extends: 8.5 in Height: 9.5 in H/CTR: 6-7/8 in

Clear Glass Cylindrical Width: 5 in Height: 6-11/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 5.12" W., 1" ht., 5.12" depth		LED: 17.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	