

Project:		
Fixture Type:		
Location:		
Contact:		

P560341-31M Parrish

Parrish Collection One-Light Matte Black Clear and Etched Glass Modern Craftsman Outdoor Small Wall Lantern

Category: Outdoor

Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Panel



Width: 4-5/8 in Extends: 6 in Height: 10 in H/CTR: 6-5/8 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.5" W., 5.5" ht., 0.75" depth		LED: 12.5-watt MAX per socket	
,		Fully dimmable with dimmable bulbs	