

Project:			
Fixture Type	::		
Location:			
Contact:			

## P560342-31M

## **Parrish**

Parrish Collection One-Light Matte Black Clear and Etched Glass Modern Craftsman Outdoor Medium Wall Lantern

Category: Outdoor

Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Panel



Width: 6.5 in Extends: 7 in Height: 14 in H/CTR: 10-1/4 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Company agreement 4"		Incandescent: 60-watt MAX per	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 5.5"		LED: 12.5-watt MAX per socket	
ht., 0.75" depth		228. 12.0 Water 17 or per 300 ket	
		Fully dimmable with dimmable bulbs	