

Project:		
Fixture Type:		
Location:		
Contact:		

P560344-031 Richmond Hill

Richmond Hill Collection One-Light Textured Black Clear Glass Modern Farmhouse Outdoor Small Wall Lantern

Category: Outdoor

Finish: Textured Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Panel



Width: 6.5 in Extends: 8 in Height: 17.5 in H/CTR: 9 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Phenolic	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 8.5" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	