

Project:			
Fixture Type:			
Location:			
Contact:			

P560345-031 Richmond Hill

Richmond Hill Collection One-Light Textured Black Clear Glass Modern Farmhouse Outdoor Medium Wall Lantern

Category: Outdoor

Finish: Textured Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Panel



Width: 8 in Extends: 9.5 in Height: 23.5 in H/CTR: 11.5 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Phenolic	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 11.62" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	