

Project:			
Fixture Type:			
Location:			
Contact:			

## P560347-169

## **Bradshaw**

Bradshaw Collection One-Light Antique Copper Clear Glass Transitional Small Outdoor Wall Lantern

Category: Outdoor

Finish: Antique Copper (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Panel



Width: 7-1/4 in Extends: 8.5 in Height: 18-1/8 in H/CTR: 8-1/8 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.5" W., 6.75" ht., 0.5" depth		LED: 12.5-watt MAX per socket	
,		Fully dimmable with dimmable bulbs	