

Project:			
Fixture Type:			
Location:			
Contact:			

## P560348-031

## **Bradshaw**

Bradshaw Collection One-Light Textured Black Clear Glass Transitional Medium Outdoor Wall Lantern

Category: Outdoor

Finish: Textured Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Panel



Width: 9.5 in Extends: 10-5/8 in Height: 24 in H/CTR: 11-1/8 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.5" W., 10.5" ht., 0.75" depth		LED: 12.5-watt MAX per socket	
,		Fully dimmable with dimmable bulbs	