

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P560348-169 Bradshaw

Bradshaw Collection One-Light Antique Copper Clear Glass Transitional Medium Outdoor Wall Lantern

**Category:** Outdoor  
**Finish:** Antique Copper (Painted)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Panel



Width: 9.5 in  
Extends: 10-5/8 in  
Height: 24 in  
H/CTR: 11-1/8 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 10.5" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	