PROGRESS LIGHTING DESIGN**+SERIES**™

Project:	
ixture Type:	
ocation:	

Contact:



Bradshaw Collection One-Light Textured Black Clear Glass Transitional Large Outdoor Wall Lantern

Category: Outdoor Finish: Textured Black (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Panel



Width: 12-3/4 in Extends: 13-7/8 in Height: 32 in H/CTR: 15-5/8 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.5" W., 1.5" ht., 0.75" depth		LED: 12.5-watt MAX per socket	
· •		Fully dimmable with dimmable bulbs	