

Project:		
Fixture Type:		
Location:		
Contact:		

P560349-169

Bradshaw

Bradshaw Collection One-Light Antique Copper Clear Glass Transitional Large Outdoor Wall Lantern

Category: Outdoor

Finish: Antique Copper (Painted) Construction: Steel Construction Glass/Shade: Clear Glass Panel



Width: 12-3/4 in Extends: 13-7/8 in Height: 32 in H/CTR: 15-5/8 in

Clear Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cETLus Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Company and a standard 42		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		555.151	
recessed outlet box: 4.5" W., 1.5" ht., 0.75" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	