



Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P560356-31M Unison

Unison Collection One-Light Matte Black Etched Seeded Glass Contemporary Wall Lantern

Category: Outdoor
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched Seeded Glass Panel



Width: 6 in
 Extends: 7-5/8 in
 Height: 18 in
 H/CTR: 9 in

Etched Seeded Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.5" W., 8" ht., 2.37" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	