

Project:		
Fixture Type:		
Location:		
Contact:		

P560357-31M

Unison

Unison Collection One-Light Matte Black Etched Seeded Glass Contemporary Large Wall Lantern

Category: Outdoor

Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Etched Seeded Glass Panel



Width: 7 in Extends: 8-5/8 in Height: 24 in H/CTR: 12 in

Etched Seeded Glass Panel

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cETLus Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 4.5" W., 8" ht., 2.37" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	