PROGRESS LIGHTING

Project:

Fixture Type:

Location:

Contact:

P560359-31M Bristol

Bristol Collection One-Light Black Modern Farmhouse Medium Outdoor Wall Lantern

Category: Outdoor Finish: Matte Black (Painted) Construction: Steel Housing Glass/Shade: Clear Beveled Glass Flat Round



Width: 7-1/2 in Extends: 4-5/8 in Height: 13-3/4 in H/CTR: 6-7/8 in

Clear Beveled Glass Flat Round

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cETLus Wet Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type Incandescent: 60-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 7.25" W.,		LED: 12.5-watt MAX per socket	
13.62" ht., 1" depth		Fully dimmable with dimmable bulbs.	