

Z-2030 LED

Wall Mounted • Wet Location Listed **PROGRESS LED**

Description:

Z-2030 LED Black Contemporary Outdoor Light

Specifications:

- Etched Glass Half Cylinder
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.75 in W, 11 in ht., 0.625 in depth
- Mounting backplate for outlet box included
- Americans With Disabilities Act (ADA) compliant
- Meets California Title 24 requirements for outdoor use

Performance:

Input Power	11 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	143/13.4 (LM-79)
CRI	90 CRI
Life (hours)	54000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Wet Location Listed

P560364-031-30



Dimensions:

Width: 7 in
Depth: 3-5/8 in
Height: 18 in

Etched Glass Half Cylinder
Width: 3-1/8 in
Height: 12-3/4 in

P560364-031-30

Dimming Notes:

P560364-031-30 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Leviton IPI06-1LZ

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron AYCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

Photometrics:

ELECTRICAL DATA	P560364-031-30
Input Voltage	120 VAC
Input Frequency	60 Hz
THD	<20%
EMI/RFI	FCC Title 47, Part 15, Class B
Operating Temperature	-30 °C to 40
Dimming	Yes*

Over-voltage, over-current, short-circuit protected

*See Dimming Notes for more information