

Z-2030 LED

Project:

Fixture Type:

Location:

Contact:

Wall Mounted • Wet Location Listed PROGRESS LED

### **Description:**

Z-2030 LED Black Contemporary Outdoor Light

### **Specifications:**

- Etched Glass Half Cylinder
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 4.75 in W., 11 in ht., 0.625 in depth
- $\boldsymbol{\cdot}$  Mounting backplate for outlet box included
- Americans With Disabilities Act (ADA) compliant
- Meets California Title 24 requirements for outdoor use

### **Performance:**

Input Power	22 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	276/13 (LM-79)
CRI	90 CRI
Life (hours)	54000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Wet Location Listed

## P560365-031-30



### **Dimensions:**

Width: 7 in Depth: 3-5/8 in Height: 28-3/4 in

Etched Glass Half Cylinder Width: 3-1/8 in Height: 23-1/2 in



## Z-2030 LED

Wall Mounted • Wet Location Listed PROGRESS LED

### **Dimming Notes:**

P560365-031-30 is designed to be compatible with many Triac/ELV controls.

The following is a partial list of known compatible dimmer controls.

#### **Dimming Controls:**

Leviton IPI06-1LZ
Leviton 6674
Lutron NTEVL-300
Lutron DVELV-300P
Lutron AYCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

### **Photometrics:**

ELECTRICAL DATA	P560365-031-30	
Input Voltage	120 VAC	
Input Frequency	60 Hz	
THD	<20%	
EMI/RFI	FCC Title 47, Part 15, Class B	
Operating Temperature	-30 °C to 40	
Dimming	Yes*	
Over-voltage, over-current, short-circuit protected		

\*See Dimming Notes for more information

# P560365-031-30