

Z-2040 LED

Wall Mounted • Wet Location Listed **PROGRESS LED**

Description:

Z-2040 Collection LED Matte Black Contemporary Medium Outdoor Wall Light
One-light LED Wall Lantern

Specifications:

- Diffused Acrylic Rectangular
- Canopy covers a standard 4" recessed outlet box: 4.5 in W., 4.5 in ht., 0.314 in depth
- Mounting backplate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Input Power	6 W
Input Voltage	120 VAC
Lumens/LPW (Delivered)	363/59.1 (LM-79)
CCT	3000 K
	3500 K
	4000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
Warranty	5-year Limited Warranty
Labels	cETLus Wet Location Listed
THD	<20%
Operating Temperature	-30 °C to 30
Dimming	No

P560367-31M-CS



Can be installed with or without canopy

Dimensions:

Width: 2 in (4-1/2 in with canopy)
Depth: 1-11/16 in
Height: 24 in

Diffused Acrylic Rectangular
Length: 2 in
Width: 0-7/16 in
Height: 24 in



Use your mobile phone camera to scan the QR code to open a link to a helpful installation video.

<https://www.youtube.com/watch?v=7lFwuRbTISw&t=14s>