

Project: _____
 Fixture Type: _____
 Location: _____
 Contact: _____

P560372-031
Tryon

Tryon Collection One-Light Small Black New Traditional Outdoor Wall Lantern

Category: Outdoor
Finish: Black (Painted)
Construction: EPMM Construction
Glass/Shade: Clear Panel Glass Flat Panels



Width: 7 in
 Extends: 7 in
 Height: 12-5/8 in
 H/CTR: 10-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Socket	cETLus Listed Wet Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5" W., 6.37" ht., 0.75" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	