

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P560377-031**  
**Radcliffe**

Radcliffe Collection Two-Light Large Black New Traditional Outdoor Wall Lantern

**Category:** Outdoor  
**Finish:** Black (Powder Coat)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Panel Glass Flat Panels



Width: 7 in  
Extends: 6-1/2 in  
Height: 24 in  
H/CTR: 11-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Socket	cETLus Listed Wet Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 6.12" W., 14.62" ht., 0.81" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	