

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P5606-104

Elina

The one-light mini-pendant from the Elina Collection spins a traditional classic and modern form by exaggerating its heirloom quality details. The fixture's tall, trumpeted opal glass, K9 glass orb accents and polished nickel finish create the distinctive silhouette.

- Traditional classic and modern form.
- Tall, trumpeted opal glass.
- K9 glass orb accents and polished nickel finish.
- Includes one 6", four 12" stems and 6 Links of chain.

Category: Pendants

Finish: Polished Nickel (plated)
Construction: Steel construction
Glass: Etched Opal glass shade



Diameter: 4-3/8" Height: 9-3/4"

Overall Ht. W/Stem: 76"

Glass

Width: 4.375" Height: 7.1875"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling stem mounted with 6 links of chain mounted Mounting strap for outlet box included 8 in of 9 gauge chain supplied One 6", four 12" lengths of stem included Canopy covers a standard 4" hexagonal recessed outlet box 5.625" W., .875" depth Includes socket ring tool	Pre-wired 10 feet of wire supplied 120 V	Quantity: One 100w Medium Base Medium base porcelain socket	UL-CUL Dry location listed 1 year warranty