

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5628-46

Arts and Crafts

One-light wall lantern with Honey Art glass and mica accent panels.

Category: Outdoor

Finish: Weathered Bronze (painted)

Construction: Die-cast aluminum construction

Glass: Honey art glass panels



Width: 6-3/4"
 Height: 10-5/8"
 Depth: 7-1/2"
 H/CTR: 2-1/4"

Glass: 1-1/32"
 Height: 4-1/8"
 Glass (2nd): 2-5/8"
 Height: 4-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" hexagonal recessed outlet box 4-1/2" sq.	Pre-wired 6" of wire supplied 120V	Quantity: 1 100W Medium Base Medium porcelain socket	UL-CUL Wet location listed 1 year warranty Companion Bath and Vanity, Chain hung lantern, Chandelier, Close-to-ceiling, Hall and Foyer, Landscape, Pendant, Post top lantern, Wall bracket, Wall lantern fixtures are available