

Cornice LED

Wall Mounted • Wet Location Listed **PROGRESS LED**

Description:

Cornice Collection One-Light LED Wall Sconce

Specifications:

- Black Cast Aluminum Shade
- White Acrylic Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" recessed outlet box: 4.5 in W., 4.75 in ht., 0.5 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	623/69.2 (LM-82)
Lumens/LPW (Delivered)	352/49.6 (LM-79)
CCT	3000 K
CRI	90+ CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30 °C
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed

P5635-3130K9



Dimensions:

Width: 6-1/8 in
Depth: 4 in
Height: 5 in
H/CTR: 2-3/8 in

Black Cast Aluminum Shade
Length: 6.0625 in
Width: 4-1/16 in
Height: 4-15/16 in

White Acrylic Diffuser
Width: 2-7/8 in
Height: 0-11/16 in

P5635-3130K9

Dimming Notes:

P5635-3130K9 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Nova T NTELV-300

Lutron_Vierti VTELV-600

Lutron_Maestro MAELV-600

Lutron_spacer/system SPSELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.