

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P5642-20 Cylinder

6" uplight/downlight wall cylinders are ideal for a wide variety of interior and exterior applications including residential and commercial. The aluminum Cylinders offers a contemporary design with its sleek cylindrical form and elegant Antique Bronze finish, perfect for today's inspired exteriors. Modern details feature a die-cast aluminum wall bracket and heavy-duty aluminum framing - resulting in an impeccable modern accent that adds panache and sophistication to your outdoor spaces. Provides even illumination up and down.

- Antique Bronze finish.
- Powder coat finish.
- Wet location listed when used with P860046 top cover lens.
- Die-cast aluminum wall brackets and heavy duty aluminum framing.
- Two 250w PAR-38 or 150w BR-40.

**Category:** Outdoor

**Finish:** Antique Bronze (Powder Coat Paint)

**Construction:** cast aluminum Construction



Width: 6 in  
Height: 18 in  
Depth: 8-7/8 in  
H/CTR: 8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: two 250 W max. PAR-38 or LED equivalent	UL-CUL Damp Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	E26 base porcelain sockets	1-year Limited Warranty
back plate covers a standard 4" recessed outlet box: 4.5" W., 4.5" ht., 2.911" depth	120 V		