

Project:			
Fixture Type:			
Location:			
Contact:			

## P5644-30

## **Square**

6" outdoor two-light up/down square with heavy duty aluminum construction and die cast wall bracket. Powder coated finish. White finish. Wet location listed when used with P860047 top cover lens (sold separately).

- · White finish.
- · Powder coat finish.
- · Ideal for a wide variety of interior and exterior applications.
- Wet location listed when used with P860047 top cover lens (sold separately).
- Two 250w PAR-38 or 150w BR-40.

**Category:** Outdoor **Finish:** White (White)

Construction: Aluminum Construction



Width: 6 in Height: 18 in Depth: 8-7/8 in H/CTR: 8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	UL-CUL Damp Location Listed
		two 250 W max. PAR-38 or LED	
Mounting strap for outlet box	6 inches of wire supplied	equivalent	1-year Limited Warranty
included			•
	120 V	E26 base porcelain sockets	
back plate covers a standard 4"			
recessed outlet box: 4.5" W., 4.5"			
ht., 2.911" depth			