

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P5644-31 Square

6" outdoor two-light up/down square with heavy duty aluminum construction and die cast wall bracket. Powder coated finish. Black finish. Wet location listed when used with P860047 top cover lens (sold separately).

- Black finish.
- Powder coat finish.
- Ideal for a wide variety of interior and exterior applications.
- Wet location listed when used with P860047 top cover lens (sold separately).
- Two 250w PAR-38 or 150w BR-40.

**Category:** Outdoor

**Finish:** Matte Black (Painted)

**Construction:** Aluminum Construction



Width: 6 in  
Height: 18 in  
Depth: 8-7/8 in  
H/CTR: 8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: two 250 W max. PAR-38 or LED equivalent	UL-CUL Damp Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	E26 base porcelain sockets	1-year Limited Warranty
back plate covers a standard 4" recessed outlet box: 4.5" W., 4.5" ht., 2.911" depth	120 V		