

DATE:	TYPE:	
NAME:		
PROJECT:		

Incandescent

P5650-31

Ashmore

Inspired by lanterns from the Old World, the Ashmore collection incorporates handsome details, quill-scrolled arms and decorative finials. The water seeded glass is in a die-cast aluminum frame. Three-light wall lantern. Textured Black finish.

- Textured Black finish.
- Water seeded glass curved panels.
- Quill-scrolled arms and decorative finials.

Category: Outdoor

Finish: Textured Black (powder coat paint)

Construction: Die-cast aluminum Construction

Glass/Shade: Water seeded glass curved panels



Width: 8-3/8" Height: 16-1/2" Depth: 10-3/8" H/CTR: 4-1/2"

Glass

Width: 5-13/16" Height: 6.-15/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Pre-wired	Quantity:	UL-CUL Wet location listed
Mounting strap for outlet box included	6 feet of wire supplied	Three 60w max. Candelabra Base E12 base phenolic sockets	1 year warranty
Back plate covers a standard 4" octagonal recessed outlet box			
4.5" W., 9" ht.			