

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5652-31

Ashmore

Inspired by lanterns from the Old World, the Ashmore collection incorporates handsome details, quill-scrolled arms and decorative finials. The water seeded glass is in a die-cast aluminum frame. Three-light wall lantern. Textured Black finish.

- Textured Black finish.
- Water seeded glass curved panels.
- Quill-scrolled arms and decorative finials.

Category: Outdoor

Finish: Textured Black (powder coat paint)

Construction: Die-cast aluminum Construction

Glass/Shade: Water seeded glass curved panels



Width: 8-3/8"
Height: 26-1/4"
Depth: 12-3/8"
H/CTR: 19-1/8"

Glass

Width: 15-13/16"

Height: 6.-15/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" octagonal recessed outlet box 5" W., 14" ht.	Pre-wired 6 feet of wire supplied 120 V	Quantity: Three 60w max. Candelabra Base E12 base phenolic sockets	UL-CUL Wet location listed 1 year warranty