

Project:			
Fixture Type:			
Location:			
Contact:			

## **P5675-31** Cylinder

 $5^{\prime\prime}$  up/down cylinder/ outdoor lantern in Black. with heavy duty aluminum construction and die cast wall bracket. Powder coated finish. Wet location listed when used with P860045 top cover lens.

- · Black finish.
- · Powder coat finish.
- · Ideal for a wide variety of interior and exterior applications.
- · Die-cast aluminum wall brackets and heavy duty aluminum framing.
- Wet location listed when used with P860045 top cover lens (sold separately)

Category: Outdoor

Finish: Black (powder coat paint)

Construction: cast aluminum Construction



Width: 5 in Height: 14 in Depth: 7-7/8 in H/CTR: 7 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: two 75 W max. PAR-30 or BR-30	cCSAus Damp Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	or LED equivalent	1-year Limited Warranty
	120 V	E26 base porcelain sockets	
back plate covers a standard 4" recessed outlet box: 4.5" W			