

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Compact fluorescent

P5686-108

Crawford

One-light wall lantern with etched flat glass panels and scroll arm details. The cast aluminum lantern is energy efficient and has a powder coat finish for durability. Oil Rubbed Bronze finish.

- Oil Rubbed Bronze finish.
- Etched white glass panels.
- Scroll arm details.
- Cast aluminum.
- Meets California Title 24.

Category: Outdoor

Finish: Oil Rubbed Bronze (painted)

Construction: Die-cast aluminum Construction, solid brass interior components

Glass/Shade: Etched white glass panels



Width: 8-7/16"
Height: 16-3/4"
Depth: 11-1/8"
H/CTR: 9-5/8"

Glass

Width: 1-1/16"

Height: 6-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Back plate covers a standard 4" octagonal recessed outlet box 4.5" W., 9" ht., 0.9619" depth	Pre-wired 6" of wire supplied 120 V	Quantity: One 26w max. GU-24 GU24 base plastic socket	cCSAus Wet location listed 1 year warranty Meets California Title 24 high efficacy requirements for outdoor use only