

Project:		
Fixture Type:		
Location:		
Contact:		

P5686-31MD Crawford

This wall lantern offers updated traditional styling with scroll arm. Etched seeded glass panes give off a soft glow of light. The panes are housed in a handsome black frame.

- Etched seeded glass panes give off a soft glow of light.
- The panes are housed in a handsome black frame.
- This wall lantern offers updated traditional styling with scroll arm.
- · Ideal for any foyer, bedroom, entryway, porch, or patio.
- · Perfect for transitional or new traditional settings.
- Measures 8-1/2-inch width by 16-3/4-inch height.
- Uses one medium base bulb that is sold separately (100w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Outdoor Finish: Black (Painted)

Construction: Cast Aluminum Construction

Glass/Shade: Etched glass Panel, Etched glass Panel



Width: 8-1/2 in Height: 16-3/4 in Depth: 11 in H/CTR: 9-5/8 in

Etched glass Panel Width: 1-11/16 in Height: 6-1/4 in

Etched glass Panel Width: 3-7/8 in Height: 6-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity: One 100 W max. Medium Base or	CCSAus Wet Location Listed
Mounting strap for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain socket	
Canopy covers a standard 4" recessed outlet box: 4.5" W., 9" ht., 0.812" depth			