

DATE:	TYPE:	
NAME:		
PROJECT:		

Compact fluorescent

## P5694-60

## **Hard-Nox**

Energy efficient, long-lasting lamps. White ribbed polycarbonate diffuser. Can be wall mounted. 120V HPF ballast. UL listed for wet locations.

Category: Outdoor Finish: White

**Construction:** Steel construction **Glass:** White ribbed polycarbonate



Width: 5-3/4" Height: 8-1/4" Depth: 4-3/8" H/CTR: 4-1/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted  Mounting strap for outlet box included  Unit covers a standard 4" hexagonal recessed outlet box	6" of wire supplied 120V HPF magnetic 120V	Quantity: 1 9W 2-pin, twin compact fluorescent G23 socket	UL-CUL Wet location listed  1 year warranty  Companion fixtures are available